

Refrigerated Heating Bath with air-cooled refrigerating unit and KISS-Controller. Consisting of isolated cooling bath made of stainless steel with immersion thermostat. Powerful pressure and suction pump made of industrial plastic material. Wetted parts made from stainless steel or plastics. With adjustable overtemperature protection according to DIN 12876.

KISS controller:

The controller combines state-of-the-art technology with simple operation. Models with KISS controller are suitable for routine tasks in research and industry and are convincing as practice oriented basic equipment:

- * Large, bright OLED display
- * Simple operation with menu navigation
- * Simultaneous display of set point, internal temperature, Tmin and Tmax
- * Status displays for pump, cooling and heating
- * USB (Device) and RS232 interfaces
- * Overtemperature protection, Safety class 3 (FL)
- * Autostart function for power failure
- * 3 colour versions available: grey (standard), blue, red

Option: Pt100 sensor connection #10688 to display (not control) e.g. of the process temperature (only available factory fitted, additional charge).

4-year warranty - registration required.

Technical data according to DIN 12876

Operating temperature range	-20...200 °C	
Temperature stability at 70°C	0,05 K	
temperature set point / display	digital	Order-No.: 2009.0021.98
Absolute accuracy	setup for calibration	
Internal temperature sensor	Pt100	
Interface digital	USB (Device), RS232 Interface	
Alarm message	optic, acoustic	
Safety classification	III / FL	
Heating power	1,5 kW	
Cooling power		
at 20°C	0,25 kW	
at 0°C	0,2 kW	
at -10°C	0,12 kW	
at -20°C	0,05 kW	
Refrigeration machine	air-cooled, natural refrigerant	
Refrigerant (ASHRAE, GHS)	R-290 (A3, H220)	
Global Warming Potential (GWP)	0,02	
Refrigerant quantity	0,041 kg	
CO2 equivalent	0,0 t	
Pressure / Suction pump		
max. delivery	14 l/min	
max. delivery pressure	0,25 bar	
max. delivery (suction)	10,5 l/min	
max. delivery pressure (suction)	0,17 bar	
Bath volume	10,5 l	
Width bath opening WxD	290x152 mm	
Bath depth	150 mm	
Height of bath opening	265 mm	
Overall dimensions WxDxH **	350x560x430 mm	
Net weight	28 kg	
Power supply requirement	110-115V 1~ 50/60Hz	
max. current immersion thermostat	15 A	
max. current refrigerated bath	2,6 A	
min. Fuse	10A	
max. Fuse	16A	
Degree of Protection	IP20	
min. ambient temperature	5 °C	

Technical data according to DIN 12876

max. ambient temperature 40 °C

from Serial-No.: **S452707** **1.1/20**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Included Accessories:

data cable #9472, bath bridge #19596.

Optional accessories:

Pump adaptor #19607, drain valve #6839, temperature control / - connection hoses, thermofluids, various bath cover and further accessories, etc.: see catalog.

Output data valid for: Room temperature 20° C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Special Case: Acetone and Polyglycol: The plastic pump is not resistant against acetone and polyglycols (depending on the manufacturer).

It is recommended that water is mixed with either glysantine or ethylene glycol for freeze protection. A more resistant plastic is available on request at an additional cost.

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

** Please respect space requirements. See operating conditions at www.huber-online.com