

Refrigerated Heating Circulator Bath with water-cooled cooling machine. Powerful, variable speed, pressure and suction pump, evaporator (cooler) and housing of stainless steel, CFC and H-CFC free. With adjustable overtemperature protection according to DIN 12876.

**Pilot ONE:**

The Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, ZH, PT, JA, CS, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

4-year warranty - registration required.

The dimensions specified below are approximate and may be subject to change.

**Technical data according to DIN 12876**

Operating temperature range	-50...200 °C	
Temperature stability at -10°C	0,02 K	
temperature set point / display	5,7" colour Touchscreen	<b>Order-No.: 2020.0015.01</b>
Internal temperature sensor	Pt100	
Sensor external connection	Pt100	
Interface digital	Ethernet, USB (Host u. Device), RS232	
Safety classification	III / FL	
Heating power	3 kW	
Cooling power		
at 100°C	2,4 kW	
at 20°C	2,4 kW	
at 0°C	2,4 kW	
at -20°C	1 kW	
at -40°C	0,4 kW	
Refrigeration machine	air- water-cooled, natural refrigerant	
Refrigerant (ASHRAE, GHS)	R-1270 (A3, H220)	
Global Warming Potential (GWP)	0	
UN-number	UN 3358	
Pressure pump	yes	
max. delivery	25 l/min	
max. delivery pressure	0,7 bar	
Suction pump	yes	
max. delivery (suction)	18,5 l/min	
max. delivery pressure (suction)	0,4 bar	
Pump connection	M16x1 male	
max. permissible kin. viscosity	50 mm <sup>2</sup> /s	
Cooling water connection	G1/2 male	
min. cooling water differential pressure	3 bar	
max. cooling water pressure	6 bar	
Bath volume	18 l	
min. filling capacity	16 l	
Bath capacity with displacement rack	11 l	

## Technical data according to DIN 12876

---

Width bath opening WxD / bath depth	270 x 150 / 200 mm
Height of bath opening	815 mm
Overall dimensions WxDxH **	455x515x1014 mm
Power supply requirement (3 phase)	400V 3~N 50Hz
Degree of Protection	IP20
max. ambient temperature	40 °C
min. ambient temperature	5 °C

---

from Serial-No.:

1.0/24

---

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Output data valid for: Room temperature 20°C, cooling water inlet 15°C and 3 bar differential pressure between cooling water inlet and outlet. This temperature control unit is designed to operate with cooling water intake temperature between 5°C and 20°C. When cooling water temperatures fall below the condensation point, it is essential to insulate the cooling water pipes in the unit.

As the cooling water temperature increases, drop in the cooling power should be expected, and also an increased cooling water flow rate possible. Materials used in the cooling water circuit include; copper, Stainless steel 1.4401, MS, PA, PPE, PTFE and EPDM. Please use suitable cooling water.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

\*\* Please respect space requirements. See operating conditions at [www.huber-online.com](http://www.huber-online.com)